PHILIPS Lighting



Core & Coil (71A) HPS 200W - 400W

CORE & COIL HID HPS BAL 250W S50 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S50
Lamp Type	250W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A8271
Core Size	4 x 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI501-H4
Ignitor Temperature Rating	105°C
Capacitor Value	35 MFD
Capacitor Catalog Number	7C350P24RA
Capacitor Requirements	240V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.65 in
Capacitor Height	3.7 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V


Input Frequency	60 Hz					
Input Current (Open Circuit)	1.53/0.95/0.77/0.63 A					
Input Current (Starting)	1.61/0.89/0.8/0.68 A					
Input Current (Short Circuit)	1.16-1.74/0.64-0.96/0.56-0.85/0.49-0.74 A					
Secondary Short Circuit Current	3.65-4.45 A					
Constant Wattage Deviation	Within Trapezoid					
Ballast Factor (Nom)	1					
Power Factor (Nom)	0.90					
Open Circuit Voltage	187 V					
Input Current (Nom)	2.5/1.47/1.25/1.09 A A					
Input Power (Nom)	295 W					
Rated Lamp Power	250 W					
Wiring						
Wire Striplength	0.5 mm					
Wire Length by Color	12"					
Wire Type	Stranded					
Remote Wiring Configuration Allowed	Yes					
Max Ballast-Lamp Distance Remote	2'					
Wiring						

Core & Coil (71A) HPS 200W - 400W

Recommended Fuse Value	7/4/4/3 A				
Approval and Application					
Open Circuit Voltage Test (Volts)	170-205 V				
Approval Marks	ULR CSA certificate RoHS Compliant				
Temperature Marking	B/B/B/B				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029B				

ORE & COIL HID HPS BAL 250W S50 QUAD KIT
81087827116
13700556609
13700556609
.176 kg
8

Dimensional drawing



HPS BAL 250W S50 QUAD C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 250W S50	3.82 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
QUAD KIT						



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change