

Eaton 736V-BOX

Catalog Number: 736V-BOX

Eaton residential grade duplex receptacle, #14-12 AWG, 15A, Residential, Flush, 125V, Side wire, Ivory, Brass, Thermoplastic, 1-15R, Duplex, Screw, Thermoplastic, ED Box



General specifications

Product Name

Eaton residential grade duplex receptacle

Catalog Number

736V-BOX

UPC

032664750670

Product Length/Depth

1.31 in

Product Height

4.19 in

Product Width

0.74 in

Product Weight

0.12 lb

Warranty

Refer to warranty document.

Certifications

cULus Listed

Federal Specification Classification 6221
02

Product specifications

Device type

Receptacle

Color

Ivory

Face/body material

Thermoplastic

Wiring method

Side wire

Features

Non-grounding

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Duplex receptacle

Device grade

Standard grade

NEMA configuration

1-15R

Style type

Standard

Design type

Straight blade

Connection type

Screw

Number of wires

Resources

Catalogs

[Residential Buyers Guide B-26](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 736V-BOX](#)

2

Receptacle type

Duplex

Voltage rating

125V

Application

Residential

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)