

## Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

## Ordering Information

Description	Form Size	Cable	UPC	Catalog Number
Straight Male Thread, F5 Stainless Steel Mesh, Liquidtight		.875"-1.000" (2.22-2.54)	783585322063	07401025

## Listings

UL Listed  
CSA Certified

## Specifications


Strand	Stainless Steel
Body	Aluminum

## Performance

### Environmental

Flammability UL 94HB (Strand grip), UL 94V-2(Fitting)  
Hazardous Locations Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

Operating Temperatures -30°F to +240°F (-34°C to +115°C)  
Wet Locations Suitable for use in wet locations when used with a listed sealing ring between box and fitting



## Related Products

Locknut	00322003LPK50
Metal Clad Sealing O-Ring	20509003

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions