

# Eaton 7501V

Catalog Number: 7501V

Eaton standard grade decorator switch, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 627569



## General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7501V
UPC	Product Length/Depth
032664627569	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.01 lb	NAFTA
	RoHS Compliant
Certifications	
cULus Listed	

## Product specifications

### Switch type

Single-pole

### Phase

Single-phase

### Load type

ELV

HAL

MLV

CFL

Motor Control

FLR

Fan

INC

LED

### Closure type

Maintained

### Color

Ivory

### Wiring method

Back and push

### Material

Thermoplastic

### Mounting method

Flush

### Allowable wire size

#14-12 AWG

### Amperage Rating

15A

### Number Of Poles

Single-pole

### Type

Switch decorator

### Voltage rating

120/277 V

### Actuator

Decorator

## Resources

### Brochures

[Decorator standard grade switches spec sheet](#)

### Specifications and datasheets

[Eaton Specification Sheet - 7501V](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)