# Eaton 7501W-BOX

## Catalog Number: 7501W-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, White, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 752360

#### General specifications



Catalog Number

Eaton standard grade decorator switch

7501W-BOX

**UPC** 

Product Length/Depth

032664752360

1.44 in

**Product Height** 

Product Width

4.19 in

0.97 in

Product Weight

Compliances

0.001 lb

NAFTA RoHS Compliant

Certifications

cULus Listed



### Product specifications

Special features

Box

Switch type

Single-pole

Phase

Single-phase

Load type

ELV

Fan

HAL

Motor Control

CFL

INC

LED

MLV

FLR

Closure type

Maintained

Color

White

Wiring method

Back and push

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

**Number Of Poles** 

Single-pole

Type

Switch decorator

Voltage rating

120/277 V

#### Resources

**Brochures** 

Decorator standard grade switches spec sheet

Specifications and datasheets

Eaton Specification Sheet - 7501W-BOX

Decorator



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia