

Eaton 7503A

Catalog Number: 7503A

Eaton standard grade decorator switch, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Almond, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 627620



General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7503A
UPC	Product Length/Depth
032664627620	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.01 lb	NAFTA
	RoHS Compliant
Certifications	
cULus Listed	

Product specifications

Switch type

Three-way

Phase

Single-phase

Load type

ELV

HAL

MLV

Fan

Motor Control

INC

LED

CFL

FLR

Closure type

Maintained

Color

Almond

Wiring method

Back and push

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Three-way

Type

Switch decorator

Voltage rating

120/277 V

Actuator

Decorator

Resources

Brochures

[Decorator standard grade switches spec sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - 7503A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)