

Eaton 7504A-BOX

Catalog Number: 7504A-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Almond, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscmt, Halogen, Four-way, Thermoplastic



General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7504A-BOX
UPC	Product Length/Depth
032664644665	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.001 lb	RoHS Compliant
	NAFTA
Certifications	
cULus Listed	

Product specifications

Special features

Box

Switch type

Four-way

Phase

Single-phase

Load type

Fan

FLR

HAL

MLV

CFL

INC

Motor Control

ELV

LED

Closure type

Maintained

Color

Almond

Wiring method

Back and push

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Four-way

Type

Switch decorator

Voltage rating

120/277 V

Resources

Catalogs

[Residential Buyers Guide B-04](#)

Specifications and datasheets

[Eaton Specification Sheet - 7504A-BOX](#)

Actuator
Decorator



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)