

Eaton 7565K5

Catalog Number: 7565K5

General Purpose AC Rated Toggle Switches, Circuit Number: D, 0.469 in bushing, Circuit position: ON-NONE-ON, 0.563 in lever, 15A at 125V, 10A at 250V, 0.75 hp at 125-250V, Solder lugs, Two-pole, Double-throw

General specifications

Product Name	Catalog Number
General Purpose AC Rated Toggle Switches	7565K5
	UPC
	786685680385
Product Length/Depth	Product Height
1.312 in	1.2 in
Product Width	Warranty
0.75 in	Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized



defaultTaxonomyAttributeLabel

Amperage Rating

15A at 125V, 10A at 250V

Horsepower

0.75 hp at 125-250 V

Number Of Poles

Two-pole

Bushing length

0.469 in

Circuit number

D

Circuit position center

None

Circuit position down

On

Circuit position up

On

Lever length

0.563 in

Terminals

Solder lug

Throw type

Double-throw

Resources

Catalogs

[Eaton's Volume 11—Vehicle and Commercial Controls](#)

Specifications and datasheets

[Eaton Specification Sheet - 7565K5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)