



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



75713 Stinger Led - 120V/100V Ac/12V DC - 2 Holders

Streamlight, Inc.

| | |
|------------------|--|
| Catalog Number | 75713 |
| Manufacturer | Streamlight, Inc. |
| Description | Rechargeable Flashlight, Rechargeable, Compact, Industrial Type; Black Color; UI (Canada and Us), Etl (Canada and Us), Ansi/UI 913, Ce, Msha Approval; Machined Anodized Aluminum Body Material; Led Lamp Type; 1 Battery(S); Stinger[R] Brand |
| Weight per unit | 2.2 (lbs/each) |
| Product Category | Flashlights, Lanterns, Warning |

Features

| | |
|---------------------|-----|
| Lamp Type | LED |
| Number of Batteries | 1 |

Material, Color, and Finish

| | |
|---------------|----------------------------|
| Body Material | Machined Anodized Aluminum |
| Color | Black |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information

Battery Type 3.6 Volt Nickel Cadmium, Nickel Metal Hydride; Size 1.17 Inch Diameter x 8.41 Inch Length; Voltage Rating 120 Volt AC/12 Volt DC; Initial Intensity 85 to 350 Lumen; Light Output 6000 to 24000 Candela; Range of Light/Distance 310 Meter; Runtime

Commodity Description

FLASHLIGHTS, LANTERNS, WARNING LIGHTS

Description

STINGER LED - 120V/100V AC/12V DC - 2 HOLDERS

extra long description

RECHARGEABLE, COMPACT, INDUSTRIAL TYPE; BLACK COLOR; UL (CANADA AND US), ETL (CANADA AND US), ANSI/UL 913, CE, MSHA APPROVAL; MACHINED ANODIZED ALUMINUM BODY MATERIAL; LED LAMP TYPE; 1 BATTERY(S); STINGER[R] BRAND; BATTERY TYPE 3.6 VOLT NICKEL CADMIUM, NICKEL METAL HYDRISE; SIZE 1.17 INCH DIAMETER X 8.41 INCH LENGTH; VOLTAGE RATING 120 VOLT AC/12 VOLT DC; INITIAL INTENSITY 85 TO 350 LUMEN; LIGHT OUTPUT 6000 TO 24000 CANDELA; RANGE OF LIGHT/DISTANCE 310 METER; RUNTIME 2 TO 7.25 HOUR; ENCLOSURE TYPE IPX4; IN

Long Description

RECHARGEABLE FLASHLIGHT, RECHARGEABLE, COMPACT, INDUSTRIAL TYPE; BLACK COLOR; UL (CANADA AND US), ETL (CANADA AND US), ANSI/UL 913, CE, MSHA APPROVAL; MACHINED ANODIZED ALUMINUM BODY MATERIAL; LED LAMP TYPE; 1 BATTERY(S); STINGER[R] BRAND

Product Type

Rechargeable Flashlight

Manufacturer Information

Brand

STINGER

GTIN

00080926757134

Manufacturers Part Number

75713

UPC

080926757134

Taxonomies, Classifications, and Categories

Category Description

FLASHLIGHTS AND BATTERIES

Type

Rechargeable, Compact, Industrial

Packaging

Carton

1

Package

6

Weight Per each

2.23833

Uses, Certifications, and Standards

Approval

UL (Canada and US), ETL (Canada and US), ANSI/UL 913, CE, MSHA