



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2311 East Broadway St.
79556-0000, TX Sweetwater
Phone: 325-236-6381
Fax: 325-236-6186



7580 R Duplex 15A 125V 10A 250V T/L

Pass & Seymour/Legrand

Catalog Number	7580
Manufacturer	Pass & Seymour/Legrand
Description	Receptacle Duplex 15A 125V 10A 250V Turnlok Registered
Weight per unit	0.3040 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15/10
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Poles	Consult the Factory
Voltage	125/250 V
Voltage Rating	125/250
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	4.031
Width	1.199

Descriptions

Description	R DUPLEX 15A 125V 10A 250V T/L
extra long description	P&S 7580 R DUP 15A 125V 10A 250V T/
Features	Impact Resistant, Brass Mounting Strap
Long Description	Receptacle Duplex 15A 125V 10A 250V Turnlok Registered
Product Type	R Dup 15A 125V 10A 250V T/L
Special Features	Impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength. One piece, high-grade contacts offer excellent conductivity and heat-rise resistance. Clearly marked rating on each unit's face. Single-piece mounting strap is free of easily loosened rivets found on other brands.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007758009
Manufacturers Part Number	7580
UPC	785007758009

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlok® Receptacle, Non-NEMA



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2311 East Broadway St.
79556-0000, TX Sweetwater
Phone: 325-236-6381
Fax: 325-236-6186

Trade Size

Amperage 15.0

Packaging

Carton 1

Package 50

Weight Per each 0.304

Uses, Certifications, and Standards

Application Industrial

environmental conditions Consult the Factory

Mounting WALL

nema rating Non-NEMA

standard Non-NEMA