



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353



## 7605SW 400W MH Temp Fixture

*Southwire Company*

Catalog Number	7605SW
Manufacturer	Southwire Company
Description	400W Metal Halide Light Fixture Wire Guard W/Bottom Pulse Start Type O
Weight per unit	20.9 (lbs/ft)
Product Category	Lighting

### Features

amperage rating	2.2
average life	10000
Ballast Type	ANSI M155
Base	Metal
Lamp Type	Pulse Start
Number of Lamps	1
Shape	Round
Voltage Rating	125
Wattage	400

### Material, Color, and Finish

color temperature	4000K
-------------------	-------

### Dimensions and Weight

Size	10" dia / 23" high
------	--------------------

### Descriptions

Description	400W MH TEMP FIXTURE
extra long description	SWC 7605SW LIGHT, SECURITY 400W MET
Features	Southwire™ 76058800 400W Metal Metal Halide Light Fixture wire guard wih bottom pulse start type is the perfect light for temporary job site, convention center, and industrial lighting. The type"O" 400 watt bulb lasts over 20,000 hours and emits 36,000 initial lumens. This fixture has a 6 foot wire guard and is rated for 125 volts and 400 watts.
Long Description	400W METAL HALIDE LIGHT FIXTURE WIRE GUARD W/BOTTOM PULSE START TYPE O
Product Type	Light, Security 400W Metal Halide

### Manufacturer Information

Brand	Cables & Cords
GTIN	00029892509538
Manufacturers Part Number	7605SW
UPC	029892509538



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353

## Taxonomies, Classifications, and Categories

Category Description	Outdoor HID Lighting
Type	Portable Light

## Packaging

Carton	1
Weight Per each	20.85

## Uses, Certifications, and Standards

Application	Type Portable O
standard	UL Listed