

# Specifications

Photo is representative

## Eaton 7623V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 647383

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade decorator switch
<b>CATALOG NUMBER</b>	7623V-BOX
<b>UPC</b>	032664647383
<b>PRODUCT LENGTH/DEPTH</b>	4.45 in
<b>PRODUCT HEIGHT</b>	1.88 in
<b>PRODUCT WIDTH</b>	1.5 in
<b>PRODUCT WEIGHT</b>	0.24 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cULus Listed
<b>PRODUCT TYPE</b>	Commercial grade decorator switch



Powering Business Worldwide

## Product specifications

**ALLOWABLE WIRE SIZE** #14-10 AWG

**SPECIAL FEATURES** Box

**TYPE** Switch decorator

**AMPERAGE RATING** 20A

**VOLTAGE RATING** 120/277 V

**NUMBER OF POLES** Three-way

**PHASE** Single-phase

**WIRING METHOD** Back and push

**SWITCH TYPE** Three-way

**MOUNTING METHOD** Flush

**CLOSURE TYPE** Maintained

**LOAD TYPE** INC  
Fan  
LED  
ELV  
HAL  
FLR  
CFL  
Motor Control  
MLV

**MATERIAL** Thermoplastic

**ACTUATOR** Antimicrobial paddle

**COLOR** Ivory

## Resources

[Eaton Specification Sheet - 7623V-BOX](#)

SPECIFICATIONS AND DATASHEETS

[Arrow Hart commercial specification grade AC decorator switches spec sheet](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative

## Eaton 7623V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 647383

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade decorator switch
<b>CATALOG NUMBER</b>	7623V-BOX
<b>UPC</b>	032664647383
<b>PRODUCT LENGTH/DEPTH</b>	4.45 in
<b>PRODUCT HEIGHT</b>	1.88 in
<b>PRODUCT WIDTH</b>	1.5 in
<b>PRODUCT WEIGHT</b>	0.24 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cULus Listed
<b>PRODUCT TYPE</b>	Commercial grade decorator switch



Powering Business Worldwide

## Product specifications

**ALLOWABLE WIRE SIZE** #14-10 AWG

**SPECIAL FEATURES** Box

**TYPE** Switch decorator

**AMPERAGE RATING** 20A

**VOLTAGE RATING** 120/277 V

**NUMBER OF POLES** Three-way

**PHASE** Single-phase

**WIRING METHOD** Back and push

**SWITCH TYPE** Three-way

**MOUNTING METHOD** Flush

**CLOSURE TYPE** Maintained

**LOAD TYPE** INC  
Fan  
LED  
ELV  
HAL  
FLR  
CFL  
Motor Control  
MLV

**MATERIAL** Thermoplastic

**ACTUATOR** Antimicrobial paddle

**COLOR** Ivory

## Resources

[Eaton Specification Sheet - 7623V-BOX](#)

SPECIFICATIONS AND DATASHEETS

[Arrow Hart commercial specification grade AC decorator switches spec sheet](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

