

Specifications



Photo is representative



Eaton 7624W-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, White, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Four-way, Thermoplastic 647444

General specifications

PRODUCT NAME	Eaton commercial grade decorator switch
CATALOG NUMBER	7624W-BOX
UPC	032664647444
PRODUCT LENGTH/DEPTH	1.29 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.18 in
PRODUCT WEIGHT	0.28 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed cULus Listed
PRODUCT TYPE	Commercial grade decorator switch



Powering Business Worldwide

Product specifications

ALLOWABLE WIRE SIZE #14-10 AWG

SPECIAL FEATURES Box

TYPE Switch decorator

AMPERAGE RATING 20A

VOLTAGE RATING 120/277 V

NUMBER OF POLES Four-way

PHASE Single-phase

WIRING METHOD Back and push

SWITCH TYPE Four-way

MOUNTING METHOD Flush

CLOSURE TYPE Maintained

LOAD TYPE LED
INC
HAL
ELV
MLV
FLR
Fan
CFL
Motor Control

MATERIAL Thermoplastic

ACTUATOR Antimicrobial paddle

COLOR White

Resources

[Eaton Specification Sheet - 7624W-BOX](#)

SPECIFICATIONS AND DATASHEETS

[Arrow Hart commercial specification grade AC decorator switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

