

Eaton's Wiring Devices
Decorator combination devices

Decorator Combination Devices

Space-saving architectural combination
devices add elegance and style

EATON

Powering Business Worldwide

Eaton's Decorator Combination switches add elegance to residential and light commercial applications. Decorator design features easy, smooth actuation of the rocker.



7728



7729



7730

Switch Combinations

Product description

Single pole & 3-Way
120/277V/AC

Features

- 120/277V/AC rating is ideal for incandescent or fluorescent lighting fixtures
- Thermoplastic rocker, top and backbody are virtually unbreakable to deliver years of durable performance
- Ultrasonic welding and integrated construction of the strap and body provide superior ground integrity even under heavy use
- Durable, injection molded housings and PVC resin comply with UL94 V0 flammability ratings
- Automatic grounding system eliminates the need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where a jumper is used
- Steel mounting strap is zinc-plated for added corrosion resistance
- Backwire clamps on side terminals provide for easy installation of #12 and #14 wire
- Terminal screws are backed out and ready for wiring to enhance ease of installation
- Break-off provision on switches for wiring both devices on the same circuit or on separate circuits
- Triple wipe blade contacts and double wipe ground contacts to insure long-term plug retention (TR7730)

Decorator combination switches



Catalog no.	Description	Rating		Color suffix
		Watt	V/AC	
□ 7728__	Two single-pole switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7729__	Three single-pole switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7730__	One single-pole switch w/ NEMA 5-15 receptacle	15 15	120 switch 125 receptacle	
□ 7731__	Two 3-way switches, back & side wire	15	120/277	A, BK, LA, V, W
□ 7732__	One single-pole switch w/ one 3-way switch, back & side wire	15 15	120 switch 125 receptacle	A, BK, LA, V, W
□ TR7730__	One single-pole switch with one tamper resistant NEMA 5-15R receptacle, back & side wire	15 15	120 switch 125 receptacle	A, BK, LA, V, W

Color ordering information

For ordering devices, include Catalog no. followed by the color suffix:
A (Almond), BK (Black), LA (Light Almond), V (Ivory), W (White)

A	BK	LA	V	W
(Almond)	(Black)	(Light Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 178 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/wiringdevices