

# Eaton 7731V-BOX

Catalog Number: 7731V-BOX

Eaton commercial grade combination switch, auto-grnd, Decorator, #14 - #12 AWG, 15A, resi, comm, 120/277V, bk and sd wiring, Rocker, Maint closure, Screw, Brass, Ivy, -20-60°C, (2) 3-way, dplx, thermoplas, polycrb, PVC



## General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	7731V-BOX
	UPC
	032664664892
Product Length/Depth	Product Height
1.75 in	4.25 in
Product Width	Product Weight
1.85 in	0.25 lb
Certifications	
NOM	
cULus Listed	

## Product specifications

### Special features

Auto-ground

### Connector type

Screw

### Switch type

(2) Three-way

### Configuration

(2) decorator

### Closure type

Maintained

### Color

Ivory

### Wiring method

Back and side

### Material

PVC

Thermoplastic

Polycarbonate

### Mounting method

Flush

### Allowable wire size

#14-12 AWG

### Amperage Rating

15A

### Contact type

Brass

### Type

Decorator

### Device grade

Commercial

### Style type

Duplex

### Operating temperature

-20 to 60 °C

### Number of ways

## Resources

### Brochures

[Decorator combination devices sell sheet](#)

### Specifications and datasheets

[Eaton Specification Sheet - 7731V-BOX](#)

(2) Three-way

Voltage rating

120/277 V

Application

Residential, commercial

Torque rating

12-14 lbf-inch

Actuator

Rocker



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)