

Eaton 7732V-BOX

Catalog Number: 7732V-BOX

Eaton commercial grade combination switch, auto-grnd, Decorator, #14 - #12 AWG, 15A, resi, comm, 120/277V, bk and sd wiring, Rocker, Maint closure, Screw, Brass, Ivy, -20-60°C, (1) 1-pole, (1) 3-way, dplx, thermoplas, polycrb, PVC

General specifications



Product Name	Catalog Number
Eaton commercial grade combination switch	7732V-BOX
	UPC
	032664664915
Product Length/Depth	Product Height
1.75 in	4.25 in
Product Width	Product Weight
1.85 in	0.25 lb
Certifications	
NOM	
cULus Listed	

Product specifications

Special features

Auto-ground

Connector type

Screw

Switch type

Single-pole, three-way

Configuration

(2) decorator

Closure type

Maintained

Color

Ivory

Wiring method

Back and side

Material

PVC

Thermoplastic

Polycarbonate

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Contact type

Brass

Type

Decorator

Device grade

Commercial

Style type

Duplex

Operating temperature

Resources

Brochures

[Decorator combination devices sell sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - 7732V-BOX](#)

-20 to 60 °C

Number of ways

Three-way

Voltage rating

120/277 V

Application

Residential, commercial

Torque rating

12-14 lbf-inch

Actuator

Rocker



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)