

Specifications

Photo is representative

Eaton 7738W-BOX

Eaton LED nightlight with switch, auto-grnd/LED nightlight, Decorator, #14 - #12 AWG, 15A, Residential, 120V, bk and sd wiring, Rocker, Maint closure, Screw, Brass, wht, -20-60°C, 1-pole, Photo, dplx, thermoplas, PVC, 1W

General specifications

| | |
|-----------------------------|----------------------------------|
| PRODUCT NAME | Eaton LED nightlight with switch |
| CATALOG NUMBER | 7738W-BOX |
| UPC | 032664727801 |
| PRODUCT LENGTH/DEPTH | 1.3 in |
| PRODUCT HEIGHT | 4.19 in |
| PRODUCT WIDTH | 1.08 in |
| PRODUCT WEIGHT | 0.25 lb |
| CERTIFICATIONS | cULus Listed |
| PRODUCT TYPE | LED nightlight with switch |



Powering Business Worldwide

Product specifications

| | |
|------------------------------|--|
| SPECIAL FEATURES | Auto-ground |
| TYPE | Decorator |
| AMPERAGE RATING | 15A |
| VOLTAGE RATING | 120 V |
| NUMBER OF POLES | Single-pole |
| CONFIGURATION | Horizontal dim/bright bar Push pad design |
| ILLUMINATION | LED dimmable nightlight |
| APPLICATION | Residential |
| WIRING METHOD | Back and side |
| CONTACT TYPE | Brass |
| SENSOR TYPE | Photo |
| SWITCH TYPE | Single-pole |
| MOUNTING METHOD | Flush |
| CLOSURE TYPE | Maintained |
| CONNECTOR TYPE | Screw |
| MATERIAL | Thermoplastic PVC |
| WATTAGE | 1 W |
| ALLOWABLE WIRE SIZE | #14-12 AWG |
| OPERATING TEMPERATURE | -20 to 60 °C |
| TORQUE RATING | 14 lbf-inch |
| STYLE TYPE | Duplex |
| ACTUATOR | Rocker |
| COLOR | White |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 7738W-BOX](#)

[Wallbox dimmable nightlight combination spec sheet](#)



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

