



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville
72802-0000, AR Russellville
Phone: 479-967-2303
Fax: 479-967-2306



774014 Toggle Switch, DPST, On-Off, Screw

Ideal

| | |
|------------------|---|
| Catalog Number | 774014 |
| Manufacturer | Ideal |
| Description | Ideal, Toggle Switch, Heavy-Duty, On-Off, Voltage Rating: 125, 227 Vac, Number Of Poles: 2, Amperage Rating: 20, 10 Amp, Action: DPST, Connection: Screw, 4 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles to 21 Amp 14.8 VDC DC Rating, Size: 1.300 In Length X 0.760 In Width X 0.800 In Height, Mounting: 1/2 In Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 to 185 Deg F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings, |
| Weight per unit | 0.1000 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|------------------|---|
| action | DPST |
| amperage rating | 20,10 |
| connection | Screw, 4 Terminals |
| Contact Rating | Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating |
| operating cycles | 100000 |
| Poles | 2 |
| Switch Type | Toggle |
| Voltage Rating | 125, 227 |

Dimensions and Weight

| | |
|--------|-------|
| Height | 0.800 |
| Width | 0.760 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville
72802-0000, AR Russellville
Phone: 479-967-2303
Fax: 479-967-2306

Descriptions

| | |
|------------------------|---|
| Description | TOGGLE SWITCH, DPST, ON-OFF, SCREW |
| extra long description | IDEAL 774014 SWITCH,TOGGLE,DPST,O-F |
| Features | Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC |
| Long Description | IDEAL, Toggle Switch, Heavy-Duty, On-OFF, Voltage Rating: 125, 227 VAC, Number Of Poles: 2, Amperage Rating: 20, 10 AMP, Action: DPST, Connection: Screw, 4 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating, Size: 1.300 IN Length X 0.760 IN Width X 0.800 IN Height, Mounting: 1/2 IN Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 To 185 DEG F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings, |
| Product Type | Switch, Toggle, DPST, O-F, Screw |
| Special Features | 1/2 IN Diameter Mounting Hole;Bulk Packaging Of 100 Available Upon Request;DC Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC;Dielectric Strength: 1500 V;Features: Great For Power Tool And Motor Control Switch Applications;Finish: Solid Brass/Nickel-Plated Bushings;Hp Rating: 1-1/2 HP At 125 To 250 VAC;Mechanical Life: 100000 Cycles;Operating Temperature: 32 DEG F To 185 DEG F (0 DEG C To 85 DEG C);Rugged Long-Wearing Solid Brass/Nickel-Plated Bushings |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Buchanan |
| GTIN | 00781789740140 |
| Manufacturers Part Number | 774014 |
| UPC | 781789740140 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | TOGGLE SWITCHES |
| Type | Heavy-Duty, On-OFF |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville
72802-0000, AR Russellville
Phone: 479-967-2303
Fax: 479-967-2306

Uses, Certifications, and Standards

| | |
|-------------------|--|
| Application | For Power Tool And Motor Control Switch Applications |
| Mounting | 1/2 IN Hole Diameter |
| standard | CSA, RU Listed, RoHS |