



Fluorescent Lampholders

Low Profile Long Twin Tube Lampholders

2G11 Lampholders



80-1600
Horizontal Snap-In Mounting
Multiple Bottom Push-In Wiring Ports
Metal-Spring Lamp Retainer Clip
1 5/8" H x 1 7/8" W x 7/8" Dia.
660W-600V



80-1601
Shunted Horizontal Snap-In Mounting
for Electronic Ballasts
Bottom Push-In Wiring
1 5/8" H x 1 7/8" W x 7/8" Dia.
660W-600V



80-1602
Shunted Vertical Snap-In Mounting for
Electronic Ballasts, Side Push-In Wiring
Wireways Allow Routing on Top
or Bottom of Mounting Panel
2" H x 1 1/4" W x 7/8" Dia.
660W-600V

2GX7 Lampholder



80-2350
Horizontal Screw Mount
w/Two Holes
1 1/8" H x 1 5/8" W x 1 3/4" Dia.

2G11 Lamp Support Clips



80-1603
Clear Vertical Clip
UV Stable Polycarbonate
Panel Thickness
.023 - .039 (0.58-0.99) Max.
1 5/8" H x 7/8" W x 3/8" Dia.



80-1604
Clear Horizontal Clip
UV Stable Polycarbonate
Panel Thickness
.023 - .039 (0.58-0.99) Max.
1 1/4" H x 1 5/8" W x 3/8" Dia.

4-Pin Long Twin Tube Lampholder & Clips



80-1605
4-Pin Long Twin Tube Lampholder
Molded White Thermosetting Urea
Copper Alloy, Double-Edge Contacts
Push-In Wiring
Accepts 18 AWG Leads - Solid, Solder
Dipped or Twisted, Tinned & Fused
1 7/8" H x 2 1/8" W x 7/8" Dia.
660W-600V



80-1606
Clear Plastic Horizontal Clip
Panel Thickness
.023 - .039 (0.58-0.99) Max.
1 1/4" H x 1 5/8" W x 1/2" Dia.

T-8 Clip



80-2119
Stainless Steel Clip
for Lamp Support

Circline Clip



90-935
Circline Fluorescent
Clip