



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



806DCI2 3/4" 90D Diecast Ins Conn

Nsi Industries

Catalog Number	806DCI2
Manufacturer	Nsi Industries
Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 3/4 Inch
Weight per unit	0.2440 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes
Number of Conductors	1 Cable

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	3/4
------	-----

Descriptions

Description	3/4" 90D DIECAST INS CONN
extra long description	BPT 806-DCI2 3/4 IN 90 Deg Conn. In
Long Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 3/4 Inch
Product Type	3/4 In 90 Deg Conn. Ins. Zinc, Box Of 10
Special Features	Furnished with 2-way Phillips/Slotted Head Screw

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747168061
Manufacturers Part Number	806-DCI2
UPC	781747168061

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	3/4
------------	-----

Packaging

Carton	10
Package	50
Weight Per each	0.244



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	90 Degrees connector suitable to connect MC/FMC to box or enclosure. Insulator rated 105 degrees C. Diameter (.875" 0 min) to (1.00" 0 max)
standard	UL, CSA
Temperature Rating	105°C