



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 808DCI2 1-1/4" 90D Diecast Ins Conn

*Nsi Industries*

Catalog Number	808DCI2
Manufacturer	Nsi Industries
Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 1/4 Inch
Weight per unit	0.6480 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes
Number of Conductors	1 Cable

### Material, Color, and Finish

Finish	Ball burnish
--------	--------------

### Dimensions and Weight

Size	1-1/4
------	-------

### Descriptions

Description	1-1/4" 90D DIECAST INS CONN
extra long description	BPT 808-DCI2 1-1/4 IN Angle Conn. I
Long Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 1/4 Inch
Product Type	1-1/4 In Angle Conn. Ins. Zinc, Box Of 25
Special Features	Furnished with 2-way Phillips/Slotted Head Screw

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747168085
Manufacturers Part Number	808-DCI2
UPC	781747168085

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

### Trade Size

Trade Size	1-1/4
------------	-------

### Packaging

Carton	25
Weight Per each	0.648



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

90 Degrees connector suitable for use to connect flexible metal conduit to box or enclosure. Insulator rated 105 degrees C.

Diameter for 1.500" 0 min to 1.625" 0 max.

standard

UL, CSA

Temperature Rating

105°C