



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



809DCI2 1-1/2" 90D Diecast Ins Conn

Nsi Industries

Catalog Number	809DCI2
Manufacturer	Nsi Industries
Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 1/2 Inch
Weight per unit	1.4 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1-1/2
------	-------

Descriptions

Description	1-1/2" 90D DIECAST INS CONN
extra long description	BPT 809-DCI2 1-1/2 IN Angle Conn. I
Long Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 1/2 Inch
Product Type	1-1/2 In Angle Conn. Ins. Zinc, Box Of 5
Special Features	Furnished with 2-way Phillips/Slotted Head Screw

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747168092
Manufacturers Part Number	809-DCI2
UPC	781747168092

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1-1/2
------------	-------

Packaging

Carton	5
Weight Per each	1.3799



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	90 Degrees connector suitable for use to connect flexible metal conduit to box or enclosure. Insulator rated 105 degrees C.
standard	UL, CSA
Temperature Rating	105°C