




4 in. Square Cover, Universal Exposed Work, 2-Device, 6-in-1 Plates

By Raco
Catalog # 809U



4 in. Square Cover, Universal Exposed Work, 2-Device, 6-in-1 Plates

Features

- RACO® exposed work covers include required hardware for mounting the receptacle(s)
- RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners
- Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions
- Accommodates 1-1/4 in. drywall thickness
- Pre-galvanized steel construction

General

EU RoHS Indicator	Contact Manufacturer
Material	809U
Paintable/Stainable	Yes
Type	Exposed Cover
UPC	050169978092

Dimensions

Cubic Capacity	6.5 cu.in
Dimensions	0.563 in x 4.125 in x 4.125 in
Height	4.125 in
Length	0.563 in
Weight	0.4 lb
Width	4.125 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Packaging Type	Polybag
Pallet Quantity	3960

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Installation Manuals - RACO Crushed Corners Covers](#)
[Instruction Sheet](#)
[Sales Drawings - 809U CUS](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Service Truck Solutions](#)
[Sell Sheets - Universal Exposed Work Covers](#)
[Sell Sheets - Exposed Work Covers](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-809U-SPEC-EN | REV 5/2024