
ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



80PVC112 SCH 80 1-1/2" 10' PVC CONDUIT

HERITAGE PLASTICS

Catalog Number	80PVC112
Manufacturer	HERITAGE PLASTICS
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 1.446 in Conduit Inner Diameter, 1.900 in Conduit Outer Diameter, 10 ft Length, Made in USA, +90 °C Maximum Operating Temperature, 2250 FT/PK Package Quantity, Belled End;Corrosion Resistant:Rust Resistant:Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 80 Special Features, Intertex ETL Listed US;UL 651 and NEMA TC2 Standards Met, 1-1/2 in Trade Size, 0.200 in Wall Thickness, 0.692 lb Weight
Weight per unit	0.6920 (lbs/ft)
Product Category	PVC Sch 80 Conduit

Features

Material	PVC
Wall Thickness	0.2
Outside Diameter	1.9

Dimensions and Weight

Height	1.9
Length	120
Width	1.9

Descriptions

Description	SCH 80 1-1/2" 10' PVC CONDUIT
Features	Atkore provides the full range of PVC electrical conduit in diameters 1/2" through 8".
Long Description	1-1/2 in x 10 ft PVC Schedule 80 Conduit, Belled End
Product Type	PVC SCH80 1-1/2 X 10 Ul Be
Short Description	PVC SCH80 1-1/2 x 10 UL BE
Extra Long Description	AL-TUBE 9306 PVC SCH80 1-1/2 x 10 U

Manufacturer Information

Brand	ATKORE - ALLIED TUBE & CONDUIT
GTIN	00091111093067
Manufacturers Part Number	9306
	A53BE12
UPC	887562

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Taxonomies, Classifications, and Categories

Category Description	PVC Schedule 80 Conduit
	PVC & ENT
Type	PVC - Sch 40/80

Trade Size

Trade Size	1-1/2

Availability

Minimum Qty	10

Packaging

Carton	10
Package	2250
Weight	0.7257
Weight Per Each	0.6920 (lbs/ft)


Uses, Certifications, and Standards

Standard	UL651

PVC Rigid Schedule 80 Conduit

Atkore
Allied Tube & Conduit

- Conforms to UL 651 and NEMA TC 2
- Sunlight resistant per UL 651
- Listed for 90° C conductors or cable
- Product manufactured with one integral solvent-weld bell standard per length



Trade Size	10-foot Length		20-foot Length		Approximate Weight per 100' (lbs)
	Part Number	Crate Quantity (ft)	Part Number	Crate Quantity (ft)	
½	8005010	6,000	8005020	12,000	21
¾	8007510	4,400	8007520	8,800	28
1	8010010	3,600	8010020	7,200	41
1¼	8012510	3,300	8012520	6,600	57
1½	8015010	2,250	8015020	4,500	73
2	8020010	1,400	8020020	2,800	100
2½	8025010	930	8025020	1,860	153
3	8030010	880	8030020	1,760	205
3½	8035010	630	8035020	1,260	250
4	8040010	570	8040020	1,140	312
5	8050010	380	8050020	760	433
6	8060010	260	8060020	520	595
8*	8080010	140	8080020	280	904

Trade Size	Dimensions (in)					
	Average OD	Minimum Average ID	Minimum Wall Thickness, T	Bell Entrance A	Bell Bottom B	Bell Length C
½	0.840	0.502	0.147	0.852	0.836	1.75
¾	1.050	0.698	0.154	1.064	1.046	2.25
1	1.315	0.910	0.179	1.330	1.310	2.25
1¼	1.660	1.227	0.191	1.677	1.655	2.25
1½	1.900	1.446	0.200	1.918	1.894	2.75
2	2.375	1.881	0.218	2.393	2.369	4.00
2½	2.875	2.250	0.276	2.890	2.868	4.00
3	3.500	2.820	0.300	3.515	3.492	4.00
3½	4.000	3.280	0.318	4.015	3.992	4.00
4	4.500	3.737	0.337	4.515	4.491	5.00
5	5.563	4.713	0.375	5.593	5.553	5.75
6	6.625	5.646	0.432	6.658	6.614	6.50
8*	8.625	7.455	0.500	8.670	8.610	6.50

*UL 651 does not include 8"

Intertek