



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104



8300HGRY Compact HG Dup Rec 20A 125V Gy

Pass & Seymour/LeGrand

Catalog Number	8300HGRY
Manufacturer	Pass & Seymour/LeGrand
Description	Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 20A 125V
Weight per unit	0.2065 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Hospital Grade, Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Height	3.281
Width	.780



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104

Descriptions

Description	COMPACT HG DUP REC 20A 125V GY
extra long description	P&S 8300HGRY COMPACT HG DUP REC 20A
Features	Single Piece Plated Steel Mounting Strap
Long Description	Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 20A 125V
Product Type	Compact HG Dup Rec 20A 125V Gry
Special Features	Impact-resistant nylon face. One-piece heat-treated triple-wipe brass power contacts. Easily accessible break-off line contact connecting tab for split circuit wiring. Corrosion-resistant, zinc-plated steel strap is locked in. Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors. High strength thermoplastic back body. Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment. Auto-ground clip

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007830026
Manufacturers Part Number	8300-HGRY
UPC	785007830026

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2065

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, UL498, CSA C22.2 No. 42, FEDSPEC