



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8300HI Compact HG Dup Rec 20A 125V I

Pass & Seymour/Legrand

Catalog Number	8300HI
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back Wire Connection, Wall Mount, 1.322 In Length, 0.780 In Width, 3.281 In Height, Thermoplastic, Ivory, Impact Resistant, Corrosion Resistant, 0.2100 LB
Weight per unit	0.2065 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	Hospital Grade, Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	COMPACT HG DUP REC 20A 125V I
extra long description	P&S 8300HI COMPACT HG DUP REC 20A 1

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007830033
Manufacturers Part Number	8300HI
UPC	785007830033

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.2065

Uses, Certifications, and Standards

Mounting	WALL
Operating Temperature	-40°-60°C
standard	FEDSPEC, CULUS, UL 498, FEDSPEC