



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279



8300I HG Duplex Recp 20A 125VAC Iv

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 8300I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3 |
| Outlet Type | Straight Blade, Hospital Grade |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wall Plate Included | NO |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .900 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279

Descriptions

| | |
|------------------------|--|
| Description | HG DUPLEX RECP 20A 125VAC IV |
| extra long description | P&S 8300I HOSP GRD DUP RECEPT 20A/1 |
| Features | Single Piece Plated Steel Mounting Strap |
| Long Description | Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V |
| Product Type | Hosp GRD Dup Recept 20A/125VAC I |
| Special Features | One-piece nickel-plated brass mounting strap with integral ground. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. Exclusive patented feature, circuit label on face allows permanent circuit identification. .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007830095 |
| Manufacturers Part Number | 8300-I |
| UPC | 785007830095 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 and UL94-5 VA |
| Mounting | WALL |
| nema rating | 5-20R |
| Operating Temperature | -40°-60°C |
| standard | FEDSPEC, CULUS, cULus UL498, CSA C22.2 No. 42, FEDSPEC |