

Eaton 834B-BOX

Catalog Number: 834B-BOX

Eaton Arrow Hart extra heavy-duty industrial specification grade single receptacle, #14-10 AWG, 20A, Industrial, Flush, 277V, Side wire, Brown, Brass, Nylon, 7-20R, Single, Screw, Nylon, ED Box



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty industrial specification grade single receptacle	834B-BOX
	UPC
	032664183201
Product Length/Depth	Product Height
1.31 in	4.19 in
Product Width	Product Weight
0.94 in	0.205 lb
Warranty	Compliances
Refer to warranty document.	RoHS Compliant

Certifications

UL
Federal Specification Classification 6233
01

Product specifications

Device type

Receptacle

Color

Brown

Face/body material

Nylon

Wiring method

Side wire

Material

Nylon

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Contact material

Brass

Type

Single receptacle

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

7-20R

Style type

Standard

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Resources

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 834B-BOX](#)

Single

Voltage rating

277 V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)