Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



838 3" Plastic Bushing 25-PK

Topaz - Southwire LLC

Catalog Number	838
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Insulating Bushing, Threaded Female Type; Thermoplastic Material; 0.75 Inch; Imc/Rigid Conduit Used On; Ul, Csa Approval; 3.87 Inch Diameter; 105 Deg C Temperature Rating; 25 Per Case Standard Package; 3 Inch Trade Size
Weight per unit	0.0640 (lbs/each)
Product Category	Plastic

Features

Material	Thermoplastic
Throat Type	PLASTIC INSULATED

Dimensions and Weight

Diameter	3.87 Inch
Height	0.75 INCH

Descriptions

Commodity Description	Rigid Conduit Fittings - Plastic
Description	3" PLASTIC BUSHING 25-PK
extra long description	FEMALE THREADED TYPE; THERMOPLASTIC MATERIAL; 0.75 INCH; IMC/RIGID CONDUIT USED ON; UL (CANADA AND US) APPROVAL; 3.87 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 25 PER CASE STANDARD PACKAGE; 3 INCH TRADE SIZE; PLASTIC INSULATED THROAT TYPE; APPLICATION INDOOR, OUTDOOR
Long Description	RIGID CONDUIT INSULATING BUSHING, THREADED FEMALE TYPE; THERMOPLASTIC MATERIAL; 0.75 INCH; IMC/RIGID CONDUIT USED ON; UL, CSA APPROVAL; 3.87 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 25 PER CASE STANDARD PACKAGE; 3 INCH TRADE SIZE
Product Type	Rigid Conduit Insulating Bushing

Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338185203
UPC	751338185203

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	THREADED FEMALE

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size	3 INCH

Packaging

Carton	1
Package	25
Standard Package	25 PER CASE
Weight Per each	0.064

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	105 DEG C
Used On	IMC/RIGID CONDUIT