

Non-illuminated Light-Duty Pushbutton

8411K11

UPC:786685676364

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Combination spade and solder lug terminal.



Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Actuator Color:** Black
- **Amperage Rating:** 750 mA at 125 Vac/dc, 250 mA at 250 Vac/dc
- **Button Extension:** 0.375 in
- **Circuit Number:** A
- **Contact Configuration:** NO
- **Material:** Nylon
- **Mounting:** Bushing
- **Number Of Poles:** Single-pole
- **Terminals:** 0.250 in spade terminal
- **Throw Type:** Single-throw

Supporting documents:

- [Eaton's Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8411K11](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.

Non-illuminated Light-Duty Pushbutton

8411K11

UPC:786685676364

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Combination spade and solder lug terminal.



Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Actuator Color:** Black
- **Amperage Rating:** 750 mA at 125 Vac/dc, 250 mA at 250 Vac/dc
- **Button Extension:** 0.375 in
- **Circuit Number:** A
- **Contact Configuration:** NO
- **Material:** Nylon
- **Mounting:** Bushing
- **Number Of Poles:** Single-pole
- **Terminals:** 0.250 in spade terminal
- **Throw Type:** Single-throw

Supporting documents:

- [Eaton's Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 8411K11](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.