

Eaton 8432AN

Catalog Number: 8432AN

Eaton Arrow Hart extra heavy-duty angled plug , #12-4 AWG, 30A, Industrial range and dryer, 250V, Back wire, Gray, Brass, Nylon, 15-30P, Three-pole, four-wire, grounding, Screw, Nylon, Core pack



General specifications

Product Name

Eaton Arrow Hart extra heavy-duty angled plug

Catalog Number

8432AN

UPC

040893021164

Product Length/Depth

1.88 in

Product Height

4.3 in

Product Width

3 in

Product Weight

0.76 lb

Warranty

Refer to warranty document.

Certifications

UL

NOM

Federal Specification Classification 6221 02



Powering Business Worldwide

Product specifications

Device type

Plug

Color

Gray

Face/body material

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#12-4 AWG

Amperage Rating

30A

Number Of Poles

Three-pole

Contact material

Brass

Type

Angled plug

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

15-30P

Style type

Power, Angled body

Design type

Straight blade

Connection type

Screw

Number of wires

4

Receptacle type

Three-pole, four-wire, grounding

Voltage rating

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Specifications and datasheets

[Eaton Specification Sheet - 8432AN](#)

250V

Application

Industrial, range and dryer

Torque rating

20-24 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)