



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.
80915-0000, CO Colorado Springs
Phone: 719-559-2456
Fax: 719-867-4287



8456R 4SQ Swivel Fixture HGR *Appleton/Oz Gedney*

Catalog Number	8456R
Manufacturer	Appleton/Oz Gedney
Description	Unilets SHC Ball Type Swivel Hanger Cover, Size: 3/4 In Fixture Stem, Length: 2 In, Material: Steel and Malleable Iron, Lamp Type: Incandescent, Fluorescent, Hid, Mounting: Ceiling, Fixture Type: Incandescent, Finish: Zinc Electroplate, Cle
Weight per unit	0.5500 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

Features

Fixture Type	Incandescent
Lamp Type	Incandescent, Fluorescent, HID
Material	Steel And Malleable Iron

Dimensions and Weight

Length	2
Size	3/4 IN Fixture Stem

Descriptions

Description	4SQ SWIVEL FIXTURE HGR
extra long description	APP 8456R 3/4 SWIVEL HANGER COVER
Long Description	UNILETS SHC Ball Type Swivel Hanger Cover, Size: 3/4 IN Fixture Stem, Length: 2 IN, Material: Steel And Malleable Iron, Lamp Type: Incandescent, Fluorescent, HID, Mounting: Ceiling, Fixture Type: Incandescent, Finish: Zinc Electroplate, Cle
Product Type	3/4 Swivel Hanger Cover
Special Features	Protect fixture against wind and vibration damage; Cushion type for added protection where lighting fixtures are subjected to vibration; Ball type swivel joint permits 20 DEG swing from vertical; Support fixtures with a maximum weight of 50 LB; For use with threaded rigid metal conduit and IMC

Manufacturer Information

Brand	Appleton/Oz Gedney
GTIN	00781381539449
Manufacturers Part Number	8456R
UPC	781381539449

Taxonomies, Classifications, and Categories

Category Description	4 SQ BOXES
Type	SHC Ball Type Swivel Hanger Cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

760 Ford St.
80915-0000, CO Colorado Springs
Phone: 719-559-2456
Fax: 719-867-4287

Packaging

Carton	1
Weight Per each	0.55

Uses, Certifications, and Standards

Application	For 4 IN Square Boxes
Mounting	CEILING
standard	UL 514A, UL File Number E2527, CSA 065180