

Eaton 863::5-4CHC

Catalog Number: 863.5-4CHC

Eaton B-Line series JIC panel enclosure, 8" height, 3.5" length, 6" width, NEMA 4, Hinged cover, 4CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	863.5-4CHC
UPC	Product Length/Depth
782051740301	3.5 in
Product Height	Product Width
8 in	6 in
Product Weight	Certifications
4.5 lb	UL 50
	CSA C22.2.
	NEMA

Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

4CHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Cont. piano hinge with s.s. door clamp, panel mount

Standards

NEMA Rating

4

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 863.5-4CHC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)