
MOGUL BASE LAMPHOLDER

8694 | [Pass & Seymour](#)



FEATURES & BENEFITS

Mogul Base, porcelain, screw terminals, keyless, single pole with bushings, 4kv pulse rated. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Mogul Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 2.13"
Height: 2.56"

TECHNICAL INFORMATION

Volts: 600V
Volts (AC): 600
Watts: 1500

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No

MOGUL BASE LAMPHOLDER

8694 | [Pass & Seymour](#)



FEATURES & BENEFITS

Mogul Base, porcelain, screw terminals, keyless, single pole with bushings, 4kv pulse rated. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Mogul Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 2.13"
Height: 2.56"

TECHNICAL INFORMATION

Volts: 600V
Volts (AC): 600
Watts: 1500

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No