

MOGUL BASE LAMPHOLDER



8694 | Pass & Seymour

FEATURES & BENEFITS

Mogul Base, porcelain, screw terminals, keyless, single pole with bushings, 4kv pulse rated. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Mogul Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No CUL Listing No: No cULus: No

cURus: No Federal Spec: No UL Listing No: Yes

UL Listing No: Yes UN SPSC: 39111803

UR: No

DIMENSIONS

Diameter (US): 2.13" Height: 2.56"

TECHNICAL INFORMATION

Volts: 600V Volts (AC): 600 Watts: 1500

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA Buy American Act Status: No