

# Eaton 884 RTSCGV NK

Catalog Number: 884 RTSCGV NK

Eaton B-Line series Type 3/3R junction boxes, 8" height, 4" length, 8" width, NEMA 3R, Screw cover, RTSCGV NK enclosure, Surface mounted, Small single door, No knockout, Embossed thru holes, Galvanized steel

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series Type 3/3R junction boxes	884 RTSCGV NK
	<b>UPC</b>
	782051008456
<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	8 in
<b>Product Width</b>	<b>Product Weight</b>
8 in	4.7 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Material/finish

### Material

Galvanized steel

### Wall thickness

16 gauge

### Finish color

Unfinished

### Color

Gray

## Model

### Style

Small single door

### Model

RTSCGV NK enclosure

### Cover type

Screw

### Mounting method

Surface

### Mounting hole details

Embossed thru holes

### Special features

Rainhood,embossed mounting provisions,platedscrews

## Standards

### NEMA Rating

3R

### Country of origin

US

## Resources

### Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

### Specifications and datasheets

[Eaton Specification Sheet - 884 RTSCGV NK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)