

Eaton 886 RTSCGV NK

Catalog Number: 886 RTSCGV NK

Eaton B-Line series Type 3/3R junction boxes, 8" height, 6" length, 8" width, NEMA 3R, Screw cover, RTSCGV NK enclosure, Surface mounted, Small single door, No knockout, Embossed thru holes, Galvanized steel

General specifications



Product Name	Catalog Number
Eaton B-Line series Type 3/3R junction boxes	886 RTSCGV NK
	UPC
	782051008760

Product Length/Depth	Product Height
6 in	8 in

Product Width	Product Weight
8 in	5.7 lb

Certifications

UL 50
CSA C22.2.
NEMA

Material/finish

Material

Galvanized steel

Wall thickness

16 gauge

Finish color

Unfinished

Color

Gray

Model

Style

Small single door

Model

RTSCGV NK enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Embossed thru holes

Special features

Rainhood,embossed mounting provisions,platedscrews

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 886 RTSCGV NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)