



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



898820 Variable Temperature Heat Gun W/LCD Display

Milwaukee Electric Tool

Catalog Number	898820
Manufacturer	Milwaukee Electric Tool
Description	This Variable Temperature Heat Gun Offers A Range From 120 to 1150 Degrees Fahrenheit. The LCD Digital Readout Display Allows You to Monitor The Temperature Via A Digital Display When Precision Control Is Needed. Two Controlled Air Volumes, 10.6/ 17.6 Cu. FT. Min., Allow You to Match The Air Speed to Your Application.
Weight per unit	2.5 (lbs/each)
Product Category	Power Tools - Corded

Features

Cord Length	8.0
maximum temperature	1050
Voltage	120.0

Material, Color, and Finish

Housing Material	Nylon
------------------	-------

Dimensions and Weight

Length	11.5
--------	------

Descriptions

Description	VARIABLE TEMPERATURE HEAT GUN W/LCD DISPLAY
extra long description	MILW 8988-20 12.5AVarTmpHtGnw/LED
Features	Variable Temperature Heat Gun with LED Display
Long Description	This variable temperature heat gun offers a range from 120 to 1150 degrees Fahrenheit. The LCD digital readout display allows you to monitor the temperature via a digital display when precision control is needed. Two controlled air volumes, 10.6/ 17.6 Cu. Ft. min., allow you to match the air speed to your application.
Product Type	12.5AVARTMPHTGNW/Led

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242063031
Manufacturers Part Number	8988-20
UPC	045242063031

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage	12.5
----------	------

Packaging

Carton	1
--------	---

Weight Per each	2.455
-----------------	-------