



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 90070 Serrated Combination Flexible Bit 1/2" X 54"

*Ideal*

Catalog Number	90070
Manufacturer	Ideal
Description	Ideal, Flexible Bit, Serrated Combination, Type C, Bit Diameter: 1/2 In, Overall Length: 54 In, Shank Diameter: 3/16 In
Weight per unit	0.6000 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Shank Diameter	3/16
----------------	------

### Dimensions and Weight

Overall Length	54
----------------	----

### Descriptions

Description	SERRATED COMBINATION FLEXIBLE BIT 1/2" X 54"
extra long description	IDEAL 90-070 SERR. COMB.FLEX BIT 1
Features	Fast and aggressive, self-starting bitUltra-sharp ground threads provide increased pulling power through obstructionsDesigned for easy to tough wood
Long Description	IDEAL, Flexible Bit, Serrated Combination, Type C, Bit Diameter: 1/2 IN, Overall Length: 54 IN, Shank Diameter: 3/16 IN
Product Type	Serr. Comb.Flex Bit 1 2 X 54"
Special Features	Features: Multi-Purpose Versatile Bit For Clean Holes; Designed For Easy To Medium Wood Drilling And Light Metal; Pressure Is Needed For Starting And Pulling The Bit Through The Wood

### Manufacturer Information

Brand	Ideal
GTIN	00783250900701
Manufacturers Part Number	90-070
UPC	783250900701

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Serrated Combination, Type C

### Packaging

Carton	2
Weight Per each	0.6

### Uses, Certifications, and Standards

Application	For Easy To Medium Wood Drilling And Light Metal
standard	RoHS