

CATV Coaxial Cables



992118

RG6 Tri-Shield CATV Coax Cables

Part Number	Description	AWG	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
992118	RG6 18CCS 80%AL Tri-Shield - Tested to 3.0GHz	18 CCS	CM CL2	31 lbs	0.288"	1,000' Reel (06) 1,000' Box (46)	Black (08)



92003

RG6 Dual Shield CATV Coax Cables

Part Number	Description	AWG	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
92001	RG6 18CCS 40%AL - Tested to 3.0GHz	18 CCS	CM CL2	26 lbs	0.269"	1,000' Reel (06) 1,000' Box (46)	Black (08)
992128	RG6 18CCS 40%AL - Tested to 3.0GHz 2x Dual (siamese) construction	18 CCS	CM CL2	52 lbs	0.269" x 0.503"	1,000' Reel (06)	Black (08)
92008	RG6 18CCS Value Coax - Tested to 3.0GHz	18 CCS	CM CL2	26 lbs	0.269"	1,000' Reel (06) 1,000' Box (46)	White (01) Black (08)
92003	RG6 18CCS 60%AL - Tested to 3.0GHz	18 CCS	CM CL2	26 lbs	0.269"	1,000' Reel (06) 1,000' Box (46)	White (01) Black (08)
92083	RG6 18CCS 60%AL - Tested to 3.0GHz CMG FT-4 rated for Canada	18 CCS	CM CL2	28 lbs	0.269"	1,000' Box (46)	White (01) Black (08)
920036	RG6 18CCS 60%AL - Tested to 3.0GHz Riser Rated	18 CCS	CMR CL2R	28 lbs	0.269"	1,000' Reel (06) 1,000' Box (46)	Black (08)
921015	RG6 18CCS 80%AL - Tested to 3.0GHz Plenum Rated	18 CCS	CMP CL2P	26 lbs	0.228"	1,000' Reel (06)	White (01)
921009	RG6 18BC 80%AL - Tested to 3.0GHz Plenum Rated	18 BC	CMP CL2P	26 lbs	0.228"	1,000' Reel (06)	White (01)
921007	RG6 18BC 90%AL - Tested to 3.0GHz Plenum Rated	18 BC	CMP CL2P	27 lbs	0.233"	1,000' Reel (06)	White (01)
992479	RG6 18CCS 60%AL - Tested to 3.0GHz For direct burial use (flooded)	18 CCS	n/a	27 lbs	0.269"	1,000' Reel (06)	Black (08)
992481	RG6 18CCS 60%AL - Tested to 3.0GHz 2x Dual (siamese) construction w/17 AWG steel mess. for aerial applications	18 CCS	n/a	67 lbs	0.271" x 0.735"	1,000' Reel (06)	Black (08)



92009

RG59 Budget CATV Coax Cables

Part Number	Description	AWG	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
992101	RG59 20CCS 40%AL	20 CCS	CM CL2	22 lbs	0.239"	1,000' Box (46)	Black (08)
992109	RG59 20CCS 67%AL	20 CCS	CM CL2	23 lbs	0.239"	1,000' Box (46)	Black (08)
92006	RG59 22CCS 40%AL	22 CCS	CM CL2	20 lbs	0.239"	1,000' Reel (06) 1,000' Box (46)	Black (08)
92009	RG59 22CCS 65%AL	22 CCS	CM CL2	21 lbs	0.239"	1,000' Reel (06) 1,000' Box (46)	Black (08)