

CATV Coaxial Cables



821010

RG11 Quad Shield CATV Coax Cables

Part Number	Description	AWG	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
992165	RG11 14CCS 60/40%AL Quad - Tested to 3.0GHz	14 CCS	CL2	74 lbs	0.424"	1,000' Reel (06)	Black (08)
821010	RG11 14CCS 60/40%AL Quad - Tested to 3.0GHz Plenum Rated	14 CCS	CL2P	61 lbs	0.378"	1,000' Reel (06)	Natural (23)



821013

RG11 CATV Coax Cables

Part Number	Description	AWG	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
992155	RG11 14CCS 60%AL - Tested to 3.0GHz	14 CCS	CL2	66 lbs	0.405"	1,000' Reel (06)	Black (08)
992153	RG11 14BC 60%AL - Tested to 3.0GHz Bare Copper Center Conductor	14 BC	CL2	66 lbs	0.405"	1,000' Reel (06)	Black (08)
821013	RG11 14CCS 61%AL - Tested to 3.0GHz Plenum Rated	14 CCS	CL2P	54 lbs	0.346"	1,000' Reel (06)	White (01)
99901	RG11 14BC 65%TC Plenum Rated	14 BC	CL2P	62 lbs	0.339"	1,000' Reel (06)	White (01)



92041 921019

RG6 Quad Shield CATV Coax Cables

Part Number	Description	AWG	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
92041	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz	18 CCS	CM CL3	34 lbs	0.300"	1,000' Box (46) 1,000' Reel (06)	White (01) Black (08)
92042	RG6 18CCS Value Quad - Tested to 3.0GHz	18 CCS	CM CL3	33 lbs	0.300"	1,000' Box (46) 1,000' Reel (06)	White (01) Black (08)
992151	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz 2x Dual (Siamese) construction	18 CCS	CM CL3	66 lbs	0.300" x 0.629"	1,000' Reel (06)	Black (08)
920414	RG6 18BC 60/40%AL Quad - Tested to 3.0GHz Bare Copper Center Conductor	18 BC	CM CL3	35 lbs	0.300"	1,000' Box (46) 1,000' Reel (06)	White (01) Black (08)
920411	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz CMG FT-4 Rated for Canada	18 CCS	CM CL3	35 lbs	0.300"	1,000' Box (46) 1,000' Reel (06)	White (01) Black (08)
920413	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz Riser Rated	18 CCS	CMR CL3R	35 lbs	0.300"	1,000' Reel (06)	Black (08)
921019	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz Plenum Rated	18 CCS	CMP CL3P	32 lbs	0.272"	1,000' Reel (06)	White (01) Black (08)
99911	RG6 18BC 60/40%AL Quad - Tested to 3.0GHz Plenum Rated, Bare Copper Center Conductor	18 BC	CMP CL3P	33 lbs	0.274"	1,000' Reel (06)	Natural (23)
92071	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz For Direct Burial use (flooded)	18 CCS	n/a	34 lbs	0.300"	1,000' Reel (06)	Black (08)
992841	RG6 18CCS 60/40%AL Quad - Tested to 3.0GHz w/17 AWG steel mess. for aerial applications	18 CCS	n/a	50 lbs	0.300" x 0.424"	1,000' Reel (06)	Black (08)

Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

* Not all options are available for each product



Coleman Cable Part Legend



Put-ups	Code	Colors	Code		Code
Reel, 250 ft	04	White	01	Pink	11
Reel, 500 ft	05	Yellow	02	Purple	13
Reel, 1,000 ft	06	Orange	03	Clear	18
Reel-in-box, 1,000 ft	16	Red	04	Fluorescent	
RabbitPull™ Pull-Box, 500 ft	45	Green	05	Pink	21
RabbitPull™ Pull-Box, 1,000 ft	46	Blue	06	Ivory	22
SignaCoil™ 500 ft	55	Brown	07	Natural	23
SignaCoil™ 1,000 ft	56	Black	08	Beige	33
		Gray	09	Red Striped	
				CorraClad™	44

