## **13 FOOT S T A N D O U T** WIDE, TOUGH, & DURABLE BLADE

152

153

154

155

5



Performance and durability expected by professional tradespeople



# **13 FOOT STANDOUT**

c: 30

NG MU

100

CONDUIT BEND

### **IMPACT RESISTANT HOUSING**

OVER-MOLDED WITH A SOFT TOUCH FINISH FOR EXCELLENT GRIP — STANDS UP TO JOBSITE DEMANDS



HEAVY-DUTY, TOUGH, – DURABLE NYLON-COATING PROTECTS BLADE PRINTING AND DELIVERS LONGER BLADE LIFE



24

**CONDUIT BENDING TABLE AND 3-PHASE LAYOUT GUIDE** PRINTED ON BACK-SIDE OF TAPE FOR CONVENIENCE

SHRINK FACTO

47

5 46

## STRONG MAGNETIC DOUBLE-HOOK

0301 m27

ATTACHES TO CONDUIT AND STEEL STUDS. DOUBLE-HOOK ALLOWS FOR VIEWING THE MEASUREMENT SCALES PRINTED ON FRONT OR BACK OF TAPE

**TETHER** Capable

**RETRACTION SPEED BRAKE** CONTROLS BLADE SPEED AND PROTECTS FINGERS FROM TOUCHING BLADE UNCLUTTERED, EASY-TO-READ BOLD LINES MARKED ON BLADE EVERY 1/8-INCH

TOOL

## PERFORMANCE AND DURABILITY EXPECTED BY PROFESSIONAL TRADESPEOPLE



Cat. No.	UPC 0-92644+	Blade Length	Hook	Magnetic	Measurement Scale	Tape Print
9216	69266-6	16' (4.9m)	Double	Yes	Imperial	Double-sided
9125	69267-3	25' (7.6m)	Single	No	Imperial	One-Sided
9225	69269-7	25' (7.6m)	Double	Yes	Imperial	Double-sided
9230	69272-7	30' (9.1m)	Double	Yes	Imperial	Double-sided
9375	69271-0	7.5m (24.6')	Double	Yes	Metric and Imperial	Double-sided

\*Visit www.kleintools.com for safety warnings. Failure to follow all instructions and warnings may result in personal injury. †CE applies to #9375 only. US Patent D803711

### **Tape Measure Holders**

5195TT











5712

**3** m

CE

Holder Cat. No. UPC 0-92644+ Description **Fits Tape Measures** 5195 55078-2 Medium Leather Pouch 9216 5196 55092-8 9125, 9225, 9375, 9230 Large Leather Pouch 5195TT 55537-4 Tape Measure Holder With Ring 9216 5707 55167-3 Nylon Tape Measure Clip/Holder 9216, 9125, 9225, 9375, 9230 5712 55131-4 9216, 9125, 9225, 9375, 9230 Nylon Pouch



See our complete line of Levels & Measuring Tools www.kleintools.com

