



## 93800S

MP400 BU (PK X 6)



**Application:** Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

**Ballast Type:** M59/O

**Bulb:** BT37

**Color Temperature:** 3600 K

**Diameter:** 4.60 IN

**Initial Lumens:** 40000

**Length:** 11.50 IN

**Mean Design Lumens:** 26000

**Package Weight:** 6.75 L

**Shape:** BT37

**Type:** Metal halide lamp HID

**Voltage:** 135 V

**Warm Up Time:** 41309

**Average Life Hours:** 20000

**Base:** Exclusionary Mogul (EX39)

**Coating:** PFA

**CRI:** 65

**Effective Arc Length:** 2

**Lamp Type:** Metal Halide

**Light Center Length:** 7 IN

**Package (LxWxH):** 14.25 IN x 9.50 IN x 12.25 IN

**Pack By:** 6

**Special Features:** Shatter-Resistant

**UPC:** 726585938001

**Wattage:** 400.0 W

ULEPH,ROHS,NSF Splash Zone



## 93800S

MP400 BU (PK X 6)



**Application:** Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

**Ballast Type:** M59/O

**Bulb:** BT37

**Color Temperature:** 3600 K

**Diameter:** 4.60 IN

**Initial Lumens:** 40000

**Length:** 11.50 IN

**Mean Design Lumens:** 26000

**Package Weight:** 6.75 L

**Shape:** BT37

**Type:** Metal halide lamp HID

**Voltage:** 135 V

**Warm Up Time:** 41309

**Average Life Hours:** 20000

**Base:** Exclusionary Mogul (EX39)

**Coating:** PFA

**CRI:** 65

**Effective Arc Length:** 2

**Lamp Type:** Metal Halide

**Light Center Length:** 7 IN

**Package (LxWxH):** 14.25 IN x 9.50 IN x 12.25 IN

**Pack By:** 6

**Special Features:** Shatter-Resistant

**UPC:** 726585938001

**Wattage:** 400.0 W

ULEPH,ROHS,NSF Splash Zone