

STEP 5 Select Transformer

Plug-in 12V Electronic Transformers

60w AC Class II *Zero Load*

No minimum load required for operation. Ideal for 12V AC LED systems. UL 2108 flame resistant plastic enclosure. Complete with pre-installed 8 foot 18/2 cord with quick connect plug on input side. Includes optional quick connect on/off switch for easy attachment to input cord. Includes pre-installed 36" output cable with Lx Fused Plug to energize 12V Lx Cable/Track.



Part Number	Finish	Dimensions
96224S-12	Black	L: 5" W: 1.6" H: 1"
96224S-15	White	L: 5" W: 1.6" H: 1"

Wattage: 0w – 60w Class II Input: 120V AC | Output: 12V AC

60w AC Class II

UL 2108, flame resistant plastic enclosure complete with pre-installed 8 foot 18/2 cord with quick connect plug on input side. Includes optional quick connect on/off switch for easy attachment to input cord. Includes pre-installed 36" output cable with Lx Fused Plug to energize 12V Lx Cable/Track.



Part Number	Finish	Dimensions
98055-12	Black	L: 5" W: 1.6" H: 1"
98055-15	White	L: 5" W: 1.6" H: 1"

Wattage: 15w – 60w Class II Input: 120V AC | Output: 12V AC

150w AC Class I

UL 2108, flame resistant plastic enclosure. Includes terminal block for easy connection to Ambiance® Lx cable output. Complete with pre-installed 8 foot, 18/2 cord with quick connect plug input side. Includes optional quick connect on/off switch for easy attachment to input cable. Designed to be mounted vertically. Input and output are located at bottom of the unit.



Part Number	Finish	Dimensions
9458-12	Black	L: 6.25" W: 2.25" H: 1.67"

Wattage: 60w – 150w Class I Input: 120V AC | Output: 12V AC