STEP 2 Select Cable

Spools of cable specially designed with easy piercing, self-sealing insulation over stranded copper wire for use with Ambiance Lx Cable Lighting System. Markings for lampholder placement every 2". Designed to be mounted in Ambiance Lx Track.

Indoor 25' Spool (1)

Part Number	Finish	Dimensions
9469-12	Black	L: 25' W: .375" H: .187"
9469-15	White	L: 25' W: .375" H: .187"

Indoor 50' Spool (1)

Part Number	Finish	Dimensions
9470-12	Black	L: 50' W: .375" H: .187"
9470-15	White	L: 50' W: .375" H: .187"

Indoor 100' Spool (1)

Part Number	Finish	Dimensions
9471-12	Black	L: 100' W: .375" H: .187"
9471-15	White	L: 100' W: .375" H: .187"

Outdoor 100' Spool (2)

Part Number	Finish	Dimensions
9373-12	Black	L: 100' W: .375" H: .187"
9373-15	White	L: 100' W: .375" H: .187"



Indoor 500' Spool (1)

Part Number	Finish	Dimensions
9472-12	Black	L: 500' W: .375" H: .187"
9472-15	White	L: 500' W: .375" H: .187"

Indoor 1000' Spool (1)

Part Number	Finish	Dimensions
9473-12	Black	L: 1000' W: .375" H: .187"
9473-15	White	L: 1000' W: .375" H: .187"

 $^{(1)}\rm Lx~10/2~AWG~105^{\circ}~C$ cable is rated for indoor use only. Maximum wattage per length 300w at 12V; 600w at 24V. Cable is not rated to run behind walls. Check with local codes.

 $^{(2)}$ 9373-12 and 9373-15 AWG 105° C cable is rated for outdoor use only. Maximum wattage is 250w at 12V; 500w at 24V.

STEP 3 Select Track

Track

Noryl® track to support cable and lampholders. Use double faced tape (9450), track clip (9438) or screws (9862) through predilled holes to attach track to surface. Track may be flexed, notched, curved and easily cut for various applications.



Part Number	Finish	Dimensions
9435-12	Black	L: 48" W: .5" H: .25"
9435-15	White	L: 48" W: .5" H: .25"

Track with Fascia Panel

One piece Noryl® fascia panel with integral track to support cable and lampholders. Use under shelves or where system cannot be hidden behind a lip on cabinets. Track/fascia may be easily cut to various lengths. Use double faced tape (9450) track clip (9438) or screws (9862) through pre-drilled holes to attach track/fascia to surface. Use double-faced tape on glass and other smooth surfaces.



Part Number	Finish	Dimensions
9443-12	Black	L: 48" W: .875" H: 1.125"
9443-15	White	L: 48" W: .875" H: 1.125"

Quick-n-Easy Track

Track complete with pre-installed mounting screws and spacers every 6" for fast installation. Track may be flexed, notched, curved and easily cut for various applications.



Part Number	Finish	Dimensions
94035-12	Black	L: 48" W: .875" H: .5"
94035-15	White	L: 48" W: .875" H: .5"

Track with Lens

Noryl® track with clear plastic diffuser to support cable and lampholders. Use 9862 screws through pre-drilled retractor holes to attach track to surface. Clear polycarbonate lens snaps onto specially designed track. Track and lens may be cut to any length. Use with, 9428 and 9830 lampholders only, 10w maximum each. Minimum spacing 6".



Part Number	Finish	Dimensions
9874-15	White	L: 48" W: 1.875" H: 1.25"