



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



962634608 Cat 5 Black

Coleman Cable

| | |
|------------------|--|
| Catalog Number | 962634608 |
| Manufacturer | Coleman Cable |
| Description | Unshielded Twisted Pair Data Cable, 1000 FT; Solid Bare Copper Conductor Material; UI 1666, Cul, Etl, Cetl Approval; Pull Box Standard Package; Pe Insulation Material; 24 Awg Solid Conductor Size; PVC Jacket Material; Black Jacket Color |
| Weight per unit | 0.0240 (lbs/ft) |
| Product Category | Pair CBL-Non-Plenum Unshielded |

Features

| | |
|---------------------------|-------------------------|
| Attenuation | 4.3 dB/100 M at 155 MHz |
| Cable Outer diameter | 0.185 Inch |
| Capacitance | 5.6 Nanofarad/100 M |
| Category | 5E |
| Conductor Size | 24 AWG Solid |
| DC Resistance | 9.38 OHM/100 M |
| Insulation Thickness | 0.036 Inch |
| Jacket Rating | CMR |
| Number of Conductor Pairs | 4 |
| Operating Frequency | 1 to 350 MHz |

Material, Color, and Finish

| | |
|-----------------------|--|
| Conductor Material | SOLID BARE COPPER |
| Insulation Color Code | White/Blue with Blue/White, White/Orange with Orange, White/Green with Green, White/Brown with Brown |
| Insulation Material | PE |
| Jacket Color | BLACK |
| Jacket Material | PVC |

Dimensions and Weight

| | |
|--------|---------|
| Length | 1000 ft |
|--------|---------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Additional Information | ROHS Compliant; Applicable Standard ANSI 568B.2; Jacket Thickness 0.2 Inch; Application Commercial, Residential, Office Phone, Fax, Internet System |
| Commodity Description | Non-Plenum Unshld Twist-Pair Cable |
| Description | CAT 5 BLACK |
| extra long description | 1000 FT; SOLID BARE COPPER CONDUCTOR MATERIAL; UL 1666, CUL, ETL, CETL APPROVAL; PULL BOX STANDARD PACKAGE; PE INSULATION MATERIAL; 24 AWG SOLID CONDUCTOR SIZE; PVC JACKET MATERIAL; BLACK JACKET COLOR; 0.185 INCH CABLE OUTER DIAMETER; 5E CATEGORY; 0.036 INCH INSULATION THICKNESS; CMR JACKET RATING; 5.6 NANOFARAD/100 M CAPACITANCE; 9.38 OHM/100 M DC RESISTANCE; 4 CONDUCTOR PAIR(S); 1 TO 350 MHZ OPERATING FREQUENCY; 4.3 DB/100 M AT 155 MHZ ATTENUATION; WHITE/BLUE WITH BLUE/WHITE, WHITE/ORANGE WITH ORANGE, WH |
| Long Description | UNSHIELDED TWISTED PAIR DATA CABLE, 1000 FT; SOLID BARE COPPER CONDUCTOR MATERIAL; UL 1666, CUL, ETL, CETL APPROVAL; PULL BOX STANDARD PACKAGE; PE INSULATION MATERIAL; 24 AWG SOLID CONDUCTOR SIZE; PVC JACKET MATERIAL; BLACK JACKET COLOR |
| Product Type | Unshielded Twisted Pair Data Cable |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00029892367671 |
| Manufacturers Part Number | 962634608 |
| Model | 96263 |
| UPC | 029892367671 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Portable Cords, Voice, Data, Video Wire & Cable |
|----------------------|---|

Packaging

| | |
|------------------|----------|
| Carton | 1000 |
| Package | 45000 |
| Standard Package | PULL BOX |
| Weight Per foot | 0.024 |

Uses, Certifications, and Standards

| | |
|----------|-------------------------|
| Approval | UL 1666, CUL, ETL, CETL |
|----------|-------------------------|