

Incandescent Shell & Fixture Sockets

Medium Base
660W, 250V/AC

FEATURES

- Interiors have removable turn knobs.
- Hickeys and nipples are threaded for mounting on standard fixture, lamp stems or brackets.



968

Fixture Sockets

660W 250V/AC

| Description | Color | Catalog No. |
|--|-------|-------------|
| Phenolic Keyless Switch, Screw Terminals Bracket Height: 0.44" (11.1mm), Overall Height: 1.88" (47.8mm) | Black | ☐ 968 |

Listed to UL496, file no. E7430; CSA certified to C22.2, no. 42



969

Fixture Sockets

660W 250V/AC

| Description | Color | Catalog No. |
|---|-------|-------------|
| Porcelain Keyless Switch, Screw Terminals Bracket Height: 0.44" (11.1mm), Overall Height: 1.88" (47.8mm) | White | ☐ 969 |

cULus Listed to UL496, file no. E7430; NOM certified

Fluorescent Lampholders

Recessed Double Contact
660W, 600V/AC

FEATURES

- For replacement use in fluorescent lighting fixtures.
- Recessed double-contact (2500, 2501) lampholders can be used for flush or surface mounting.
- Captive pal nut for easy mounting.
- Push-in wire terminals feature release slots.
- Molded of durable white thermoset plastic.



2501W

Recessed Double Contact Lampholders

660W 600V/AC

| Description | Color | Catalog No. | |
|--|-------|-------------|---|
| Plunger Type, Push Wire Cap, Screw Switch | White | ☐ 2501W | • |
| Stationary Type, Push Wire Cap, Screw Switch | White | ☐ 2500W | • |

Listed to UL1570; CSA certified



2500W

Dimensional Information: B-64

Fluorescent Lampholder Panel Cutout Information: See page F-20

Specification Information: Please visit www.cooperwiringdevices.com

NAFTA Compliant: See page F-21