

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Insulating Bushings - Knockout

Images





Download Photo Image Download Dimensional Image

Dimension A in Inches: 1-3/8 Dimension B in Inches: 1-7/8 Dimension C in Inches: 1-3/4

Application

Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

Product Information

Material: Plastic Finish: Natural

Certifications & Codes:

CSA File Number: LR24719
NEMA Standard: FB-1
UL Standard: UL-514B
UNSPSC: 39121312

Catalog ID: 9794

UPC Number: 781747007940

Description: Bushing, Insulating, Plastic Rated 105

Degrees C, 1.750 Inch Hole Dia.

Application: Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

Trade Size: 1-1/4"

Country of Manufacture: USA

Std Pkg Qty: 500

Unit Qty: 50