



9795 1-1/2" Knock Out Insulating Bushing

Nsi Industries

Catalog Number	9795
Manufacturer	Nsi Industries
Description	Insulating Bushing, 1-1/2 In Trade Size, Black, Straight Connection Orientation, Threaded Connection, 2.125 In Width, 0.453 In Height, 2-1/8 In Diameter, +150 °C Operating Temperature, 0.0196 LB/Ea
Weight per unit	0.0196 (lbs/each)
Product Category	Plastic

Features

Material	Plastic
media	Yes

Material, Color, and Finish

Color	Black
Finish	Natural

Dimensions and Weight

Size	1-1/2
------	-------

Descriptions

Description	1-1/2" KNOCK OUT INSULATING BUSHING
extra long description	BPT 9795 1-1/2 IN Plastic Knockout

Manufacturer Information

Brand	Bridgeport
GTIN	00781747007957
UPC	781747007957

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	BUSHING

Packaging

Carton	25
Package	250
Weight Per each	0.0196



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

standard

CSA, UL

Temperature Rating

105°C