


## **Insulating Bushings - Knockout**

Images





Download Photo Image Dimension A in Inches: 1-5/8 Dimension B in Inches: 2-1/8 Dimension C in Inches: 2

**Download Dimensional Image** 

**Bridgeport Fittings Inc.** 705 Lordship Blvd. Stratford, CT 06615

> Phone: 203-377-5944 Fax: 203-381-3488

## Application

Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

## **Product Information**

Material: Plastic Finish: Natural

## **Certifications & Codes:**

CSA File Number: LR24719 NEMA Standard: UL Standard: UNSPSC:

FB-1 UL-514B 39121312

Catalog ID: 9795

UPC Number: 781747007957

Description: Bushing, Insulating, Plastic Rated 105 Degrees C, 2.000 Inch Hole Dia.

Application: Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

Trade Size: 1-1/2"

Country of Manufacture: USA

Std Pkg Qty: 250

Unit Qty: 25